

**CONTRA ANGLE
LOW SPEED HANDPIECE**

Model: CX235

(1:5, 1:1, 4:1, 10:1, 16:1, 20:1, 64:1)



Simple, effective, disassemble it without tools and can be cleaned thoroughly to avoiding cross infection

Skillful workmanship, reliable in quality

Two cooling system with dipopore atomization

Stale, quiet and large torque cartridge

Push button contra angle for implant

Specially for the european style, comfortable feeling

Technical:

| Low speed handpiece: | 1:5 speed | 16:1 speed |
|----------------------|-----------------|--------------------------------------|
| Chuck type: | push button | push button |
| Spray: | inner channel | inner channel and external |
| Bur applicable: | Ø1.6mm | Ø2.35 _{max} mm (ISO 1797-1) |
| Rotation speed: | about 20,000rpm | 40,000rpm |
| Torque: | | 70N.cm |

**INNER CHANNEL
CONTRA ANGLE**

Model: CX235

1:5 speed increase



optic fiber



Stale, quiet and large torque cartridge



Order code: C7-1
Inner channel **optic fiber**
For CA burs (Ø1.6) push button
Max speed: 20,000rpm



Order code: C7-2
Inner channel
For CA burs (Ø1.6) push button
Max speed: 20,000rpm